



Y60LW

by Burndy
Catalog ID: Y60LW

Prop 65 Notice

Hydraulic remote, 4/0 Str.-2500 kcmil Cu 3/0 Str.-2500 kcmil Al, 8.06 in W, 60 Tons, Weight 43 lbs.

- Remote power operated
- Used with BURNDY L, wide L style dies, and HPS/Fargoequivalent 60 ton dies
- Base stand and metal carry case (for head only) included
- Side lift handle
- Single Acting Ram With Heavy Duty Return Spring
- Fast Easy Die Changing And Secure Die Positioning With Positive Die Release Locking Pins

Portable, light weight design of less than 43 lbs, 60 tons of crimp force at 10,000 psi operating pressure, Single acting ram with heavy duty return spring 5 year limited warranty

Product Details

General

Application	Crimping
Crimp Force Capacity	60 ton
Die Type	L (standard or wide)
Sub Brand	HYPRESS
Tool Type	Remote Hydraulic Crimp Head
Trade Name	HYPRESS™
Type	Crimpers
UPC	781810545218
UPC 12 Digit	7818105452188

Dimensions

Height	12.93 in
Weight	43 lb
Width	8.06 in

Conductor Related

Crimping Ranges	Transmission and distribution connectors tension sleeves - Copper: 1/0 STR. - 1000 kcmil, Aluminum: 1/0 STR. - 2300 kcmil, ACSR: 1/0 STR. - 2156 (84/19 STR.); Aerial - Copper: 4/0 STR. - 2500 kcmil, Aluminum: 3/0 STR. - 2500 kcmil
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, stand and case

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)