



Y750BHXT

by Burndy
Catalog ID: Y750BHXT

Prop 65 Notice

Hydraulic remote, 12 Tons, 10000 psi, Remote Power Operated.

- 355° head rotation
- Used with U style dies
- Exposed positive die lock buttons

Easy die change out and retention with exposed positive die lock buttons, Hot stick adapter sold separately, Infinitely rotatable head, so hydraulic couplers won't easily loosen 5 year limited warranty

Product Details

General

Application	For Use On: 8 AWG Solid - 500 KCMIL Copper, 6 AWG Solid - 556.5 KCMIL Aluminum, 4 AWG - 556.5 KCMIL ACSR (Tension Sleeves), 14 AWG Solid - 500 KCMIL Copper, 6 AWG - 500 KCMIL Aluminum (Taps), 6 AWG - 500 KCMIL Copper (Aerial Cable), 8 AWG - 750 KCMIL Aluminum And Copper, 4 AWG - 556 KCMIL ACSR (Terminals And Splices), 6 AWG - 500 KCMIL Copper (cable/ground rod), 1/2 - 1 IN Diameter Ground Rods (HYGROUND Compression Grounding)
Crimp Force Capacity	12 ton
Die Type	U DIE
Sub Brand	HYPRESS
Tool Type	Remote Hydraulic Crimp Head
Trade Name	HYPRESS™
Type	Crimpers
UPC	781810458594
UPC 12 Digit	7818104585944

Dimensions

Height	2.9 in
Jaw Width	1.70 in
Length	12.8 in
Weight	10.8 lb
Width	5.2 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)