

YA1C2NT10

by Burndy
Catalog ID: YA1C2NT10

Prop 65 Notice

#1 Long Barrel; #10 Stud; Narrow Tongue; 2-hole W/O Inspection Window.



Product Details

General

Color Code	Green
Connector Type	Terminal
Die Index	11;375
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810672549

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Bolt Hole Size inch	0.21 in
Dimension - L Length Overall mm	74 mm
Dimension - Length Overall inch	2.90 in
Dimension - Pad Width inch	0.50 in
Dimension - Strip Length inch	1-7/16 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	75 (37) Navy
Conductor - Copper Str Navy Size Range	75 (37) Navy
Conductor - Copper Str Size	1 AWG
Conductor - Copper Str Size Range	1 AWG

Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Str Navy-Size
----------------	--

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)