



YA1C2TC14

by Burndy
Catalog ID: YA1C2TC14

Prop 65 Notice

Cu Comp Terminal Code Cond, Bvl Entry, 2 Hole/W/O/InspWindow, #1 AWG Code, 75 Navy, 600 V-35 kV, 1/4" Stud, 0.62" Spacing, Lng bbl, Green, 11 or 375 Index

Product Details

General

Color Code	Green
Connector Type	Terminal
Die Index	11;375
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810019771
UPC 12 Digit	7818100197711

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - D inch	1.27 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	77 mm
Dimension - Length Overall inch	3.03 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.67 in
Dimension - Strip Length inch	1-7/16
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.34 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Solid Size	1 AWG
Conductor - Copper Solid Size Range	1 AWG
Conductor - Copper Str Navy Size	75 (37) Navy
Conductor - Copper Str Navy Size Range	75 (37) Navy
Conductor - Copper Str Size	1 AWG
Conductor - Copper Str Size Range	1 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)