

YA1CBR

by Burndy
Catalog ID: YA1CBR

Cu HYLUG™ Tubing Compression Terminal, 1 Hole W/O InspWindow, #1 AWG Code, 75 Navy, 5/16" Stud, Long Barrel, Tin Plated



Product Details

General

Color Code	Green
Connector Type	Terminal
Die Index	11;375
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Electro-Tin plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810092095
UPC 12 Digit	7818100920955

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	62 mm
Dimension - Length Overall inch	2.45 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.68 in
Dimension - Strip Length inch	1-7/16
Dimension - Z inch	0.36 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	75 (37) Navy
Conductor - Copper Str Size	1/0
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)