

# YA1CG12

by Burndy  
Catalog ID: YA1CG12

HYLUG™, 1 Hole,SKIVED, 1 AWG, Long Barrel, Un Plated



## Product Details

### General

Color Code	Green
Connector Type	Terminal
Die Index	1018
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810138397
UPC 12 Digit	7818101383977

### Dimensions

Dimension - B Length fraction	15/16 in
Dimension - B Length inch	0.94 in
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.22 in
Dimension - N inch	0.44 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.67 in
Dimension - Z inch	0.44 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Size	1 AWG
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	20
-----------------------	----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)