

# YA1CL2NT14

by Burndy  
Catalog ID: YA1CL2NT14

Prop 65 Notice

Copper Compression Lug, Narrow Tongue, 2 Hole w/ Inspection Window,  
1 AWG, 1/4" Stud, 5/8" Stud Hole Spacing, Short Barrel, Tin Plated



## Product Details

### General

Color Code	Green
Connector Type	Terminal
Die Index	11
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810238103

### Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - D inch	1.26 in
Dimension - Hole Size inch	0.27 in
Dimension - L Length Overall mm	65 mm
Dimension - Length Overall inch	2.55 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.50 in
Dimension - Strip Length inch	15/16

Dimension - Stud Size inch	1/4
Dimension - Z inch	0.32 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	75 (37) Navy
Conductor - Copper Str Navy Size Range	75 (37) Navy
Conductor - Copper Str Size	1 AWG
Conductor - Copper Str Size Range	1 AWG

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)