

# YA1CLNT1490

by Burndy  
Catalog ID: YA1CLNT1490

Prop 65 Notice

1 Hole HYLUG Uninsulated Cu Compression Terminal, Narrow Tongue, #1 AWG, 600 V - 35 KV, Standard Barrl, Green



## Product Details

### General

Color Code	Green
Connector Type	Terminal
Die Index	11
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
UPC	781810167403
UPC 12 Digit	7818101674033

### Dimensions

Dimension - B Length inch	0.88 in
Dimension - D inch	0.94 in
Dimension - Hole Size inch	0.27 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.50 in
Dimension - Strip Length inch	15/16
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.69 in
Physical Attribute - Tongue Angle	90 Degree

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Solid Size	1

Conductor - Copper Solid Size Range	1
Conductor - Copper Str Size	1
Conductor - Copper Str Size Range	1

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	25
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)