

YA1CLNT14

by Burndy
Catalog ID: YA1CLNT14

Prop 65 Notice

Flex Conductor Standard Barrel Narrow, #1 AWG, 1/4 in, 2.23 in L.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Die Index: 11, Tongue Angle: Straight, Wire Strip Length: 15/16 IN, Finish: Electro-Tin Plated, Temperature Rating: 90 DEG C, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W1CVT Die, (1), Hydraulic: BCT500HS, Y500CHS Tool, X1CRT Die, (1), Y35, Y39, Y750, PAT750 Tool, U1CRT Die, (1), Y46, Tool, U1CRT Die With PUADP-1 Adapter, (1), Color Code: Green, Conductor Type: Commercial Stranded Copper, Dieless Tools (number Of Crimps): Y644HS, Y81KFT, Y81KFTMBH, PAT81KFT-18V, MY29-3, MY29-11 Tool, (1), MRC840 Tool



Product Details

General

Application	For Code Conductor
Color Code	Green
Connector Type	Terminal
Die Index	11
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	YA-L-NT, Code Conductor Standard Barrel Narrow Tongue
UPC	781810018507

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - D inch	0.94 in
Dimension - L Length Overall mm	57 mm
Dimension - Length Overall inch	2.23 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.50 in
Dimension - Strip Length inch	15/16

Dimension - Stud Size inch	1/4
Dimension - Z inch	0.69 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	75 (37) Navy
Conductor - Copper Str Navy Size Range	75 (37) Navy
Conductor - Copper Str Size	1 AWG
Conductor - Copper Str Size Range	1 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)