

YA252NT14E1

by Burndy
Catalog ID: YA252NT14E1

Prop 65 Notice

Hylug,Narrow Tongue,Double Hole W/o insp window,1/0 AWG,1/4" Stud,Pink



Product Details

General

Color Code	Pink
Connector Type	Terminal
Die Index	12;348
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810490785

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - L Length Overall mm	87 mm
Dimension - Length Overall inch	3.43 in
Dimension - Pad Width inch	0.48 in
Dimension - Strip Length inch	1-7/16
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Solid Size	1/0 AWG
Conductor - Copper Solid Size Range	1/0 AWG
Conductor - Copper Str Navy Size	100 (61) Navy

Conductor - Copper Str Navy Size Range	100 (61) Navy
Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)