

YA25A790

by Burndy
Catalog ID: YA25A790

Prop 65 Notice

Aluminium Tube Hylug; 2 Holes w/o Inspection Window; Al-1/0 AWG,Cu-1/0 AWG; 600V-35kV; 1/2" stud; Closed; Compression; 0.56 in BCD; Tan



* Representative image

Product Details

General

Connector Type	Terminal
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
UPC	781810511794
UPC 12 Digit	7818105117944

Dimensions

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG
Conductor - Copper Str Compact Size	1/0 AWG
Conductor - Copper Str Compact Size Range	1/0 AWG
Conductor - Copper Str Size	1/0

Conductor - Copper Str Size Range	1/0
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str Cmpt-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)