

# YA25G12DTS

by Burndy  
Catalog ID: YA25G12DTS

Prop 65 Notice

Cu Hylug; 1 Hole w/o Inspection Window; 1/0 STR Code; 600V-35kV; 3/8" stud; Long; Compression; 0.44 in BCD



## Product Details

### General

Connector Type	Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	HYLUG™
UPC	781810085325
UPC 12 Digit	7818100853255

### Dimensions

Dimension - B Length inch	1.38 in
Dimension - D inch	0.75 in
Dimension - Hole Size inch	0.44 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	66 mm
Dimension - Length Overall inch	2.59 in
Dimension - N inch	0.38 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.75 in
Dimension - Z inch	0.37 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0
Conductor - Material	Copper
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	100
-----------------------	-----

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)