

# YA25L2NT14E1

by Burndy  
Catalog ID: YA25L2NT14E1

Prop 65 Notice

Cu compression narrow tongue std barrel-Code conductor, 2 holes/W/ insp window, 1/0 AWG, 600V-35Kv, 1/4" stud, Pink,12 index



## Product Details

### General

Color Code	Pink
Connector Type	Terminal
Die Index	12
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810020272

### Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - D inch	1.94 in
Dimension - L Length Overall mm	83 mm
Dimension - Length Overall inch	3.28 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.48 in
Dimension - Strip Length inch	15/16
Dimension - Stud Size inch	1/4

Dimension - Z inch	0.69 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	100 (61) Navy
Conductor - Copper Str Navy Size Range	100 (61) Navy
Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)