



## YA25L4TCG1

by Burndy  
Catalog ID: YA25L4TCG1

Prop 65 Notice

Cu terminal(4 hole split pad), 4 Holes/W/insp W, 1/0 AWG, 1/4" stud, Tin plated, Pink, 12or348 Index.

Features: Compression Split Pad Terminal, Overall Length: 3.05 IN, Finish: Tin Plated

## Product Details

### General

Application	For use on copper compression connections
Color Code	Pink
Connector Type	Terminal
Die Index	12;348
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	4
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810125854
UPC 12 Digit	7818101258544

### Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - D inch	1.13 in
Dimension - F Width Center to Center inch	0.75 in
Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	77 mm
Dimension - Length Overall inch	3.05 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	1.38 in
Dimension - Strip Length inch	15/16
Dimension - Stud Size inch	1/4

Dimension - Z inch	0.20 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Navy Size	100 (61) Navy
Conductor - Copper Str Navy Size Range	100 (61) Navy
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	20
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)