

YA25L4

by Burndy
Catalog ID: YA25L4

Prop 65 Notice

Cu code conductor standard barrel, Single hole/W/ insp window, 1/0 AWG, 3/8" stud, Tin plated, Pink, 12 index.

Features: Compression Terminal, With Inspection Window, Die Index: 12 or 348, Wire Strip Length: 15/16 IN, Finish: Electro-Tin Plated, Tongue Angle: Straight



Product Details

General

Application	For Use On: UL Listed 90 DEG C, 600 Volts to 35kV ,For Code Conductor
Color Code	Pink
Connector Type	Terminal
Die Index	12;348
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG, TERMINALS
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810114759

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - D inch	0.74 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	53 mm
Dimension - Length Overall inch	2.09 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.75 in
Dimension - Strip Length inch	15/16
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.33 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	100 (61) Navy
Conductor - Copper Str Navy Size Range	100 (61) Navy
Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)