

YA262NT516

by Burndy
Catalog ID: YA262NT516

Cu compression narrow tongue std barrel-Stranded conductor, Double hole W/o insp window, 2/0 AWG, 600V-35Kv,5/16" stud,Black, 13 index



Product Details

General

Color Code	Black
Connector Type	Terminal
Die Index	13
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810672624

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.50 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - L Length Overall mm	93 mm
Dimension - Length Overall inch	3.66 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.62 in
Dimension - Strip Length inch	1-9/16 in
Dimension - Stud Size inch	5/16 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	125 (61)

Conductor - Copper Str Size	2/0
Conductor - Copper Str Size Range	2/0
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)