

YA26G13

by Burndy
Catalog ID: YA26G13

CULUG-2/OSTR-B=2-1/2STUD



Product Details

General

Connector Type	Terminal
Die Index	13
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810080290
UPC 12 Digit	7818100802900

Dimensions

Dimension - B Length fraction	2 in
Dimension - B Length inch	2.00 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - D inch	1.00 in
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	85 mm
Dimension - Length Overall inch	3.33 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	.94 in
Dimension - Z inch	0.50 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)