

# YA26L2NT14E1

by Burndy  
Catalog ID: YA26L2NT14E1

Prop 65 Notice

Cu compression narrow tongue std barrel-Code conductor, 2 holes/W/  
insp window, 2/0 AWG, 600V-35Kv, 1/4" stud, Black, 13 index



## Product Details

### General

Color Code	Black
Connector Type	Terminal
Die Index	13
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810020289

### Dimensions

Dimension - B Length fraction	15/16 in
Dimension - B Length inch	0.94 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - D inch	1.60 in
Dimension - L Length Overall mm	77 mm
Dimension - Length Overall inch	3.03 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.48 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.35 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	125 (61) Navy
Conductor - Copper Str Navy Size Range	125 (61) Navy
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## For further technical assistance, please contact us

### BURNDY Headquarters

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)