



## YA26L790BR

by Burndy  
Catalog ID: YA26L790BR

Cu Tubing Compression Terminal, 1 Hole W/InspWindow, 2/O AWG Code, 125 Navy, 5/8" Stud, 90 Deg Bent, Standard Barrel, Bare

### Product Details

#### General

Color Code	Black
Connector Type	Terminal
Die Index	13
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810091517
UPC 12 Digit	7818100915177

#### Dimensions

Dimension - B Length fraction	15/16 in
Dimension - B Length inch	0.94 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - D inch	1.33 in
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	18 mm
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.71 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.90 in
Dimension - Strip Length inch	1 in
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	90 Degree

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

## Conductor Related

Conductor - Copper Str Navy Size	125 (61) Navy
Conductor - Copper Str Navy Size Range	125 (61) Navy
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)