

## YA26T6

by Burndy  
Catalog ID: YA26T6

Prop 65 Notice

Cu Tubing Hylug, 1 Hole w/o Inspection Window, 2/0 AWG Code, 70mm<sup>2</sup> STR, 600V-35kV, 1/2" stud, Long, Compression, 0.53 in BCD, Black



## Product Details

### General

Color Code	Black
Connector Type	Terminal
Die Index	13
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810080313
UPC 12 Digit	7818100803133

### Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.50 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - Inside Diameter inch	0.43 in
Dimension - L Length Overall mm	82 mm
Dimension - Length Overall inch	3.22 in
Dimension - N inch	0.69 in
Dimension - Outside Diameter inch	0.58 in
Dimension - Pad Width inch	0.81 in
Dimension - Strip Length inch	1-9/16 in
Dimension - Thread Size	1/2
Dimension - Z inch	0.61 in
Physical Attribute - Tongue Angle	Straight

Thickness - Pad	0.13 in
-----------------	---------

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper Str Navy Size	125 (61) Navy
Conductor - Copper Str Size	70 mm <sup>2</sup> ,2/0 AWG
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	20
-----------------------	----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)