

YA272NU

by Burndy
Catalog ID: YA272NU

Prop 65 Notice

Cu Tubing Hylug (Undrilled), Blank Tongue, 3/0 AWG Code, 600V-35kV, Long, Compression, Orange



Product Details

General

Color Code	Orange
Connector Type	Terminal
Die Index	14
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	0
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810503256
UPC 12 Digit	7818105032566

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.50 in
Dimension - Bolt Size fraction	1/4, 5/16, 3/8, 7/16, 1/2
Dimension - Hole Size inch	0.266, 0.328, 0.391, 0.453, 0.525 & NEMA 0.562
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5.01 in
Dimension - Outside Diameter inch	0.62 in
Dimension - Pad Width inch	0.91 in
Dimension - Strip Length inch	1-9/16
Dimension - Stud Size inch	1/4
Physical Attribute - Tongue Angle	Straight
Thickness - Pad	0.13 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str Navy Size	150 (61) Navy
Conductor - Copper Str Size	3/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)