



YA27L2NT516

by Burndy
Catalog ID: YA27L2NT516

Prop 65 Notice

Copper Tubing,Narrow,Double Hole /W/ insp window,3/0 AWG,5/16"stud,
Tin plated,Orange,14 index

Product Details

General

Color Code	Orange
Connector Type	Terminal
Die Index	14
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810498064

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - D inch	1.73 in
Dimension - L Length Overall mm	83 mm
Dimension - Length Overall inch	3.26 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.62 in
Dimension - Pad Width inch	0.60 in
Dimension - Strip Length inch	1-1/16
Dimension - Stud Size inch	5/16
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Solid Size	3/0 AWG
Conductor - Copper Str Size	3/0 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)