

YA27L4NK

by Burndy
Catalog ID: YA27L4NK

Uninsulated Cu Compression Terminal, 1 Hole W/InspWindow, 3/0 AWG Code, 150 Navy Stranded Cu Cond, 600V - 35kV, 3/8" Stud, Nickel Plated



Product Details

General

Color Code	Orange
Connector Type	Terminal
Die Index	14
Feature - Barrel Style	<ul style="list-style-type: none"> Chamfered Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Nickel
Trade Name	HYLUG™
Type	Standard Barrel, Nickel Plated
UPC	781810163115
UPC 12 Digit	7818101631155

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	58 mm
Dimension - Length Overall inch	2.29 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.62 in
Dimension - Pad Width inch	0.91 in
Dimension - Strip Length inch	1-1/16
Dimension - Thread Size	3/8
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

Thickness - Pad	0.13 in
-----------------	---------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Navy Size	150 (61) Navy
Conductor - Copper Str Size	3/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)