

YA282NT38

by Burndy
Catalog ID: YA282NT38

Prop 65 Notice

Copper Tubing, 2 Holes W/O insp window, 4/0 AWG, 3/8" stud, Tin plated, 200 Navy, 15 index, Purple



Product Details

General

Color Code	Purple
Connector Type	Terminal
Die Index	15
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810672693

Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.62 in
Dimension - Bolt Hole Size inch	0.41 in
Dimension - Bolt Size fraction	3/8
Dimension - L Length Overall mm	101 mm
Dimension - Length Overall inch	3.99 in
Dimension - Outside Diameter inch	0.69 in
Dimension - Pad Width inch	0.76 in
Dimension - Strip Length inch	1-11/16 in
Dimension - Stud Size inch	3/8 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	200 (61)

Conductor - Copper Str Size	4/0
Conductor - Copper Str Size Range	4/0
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)