

YA28A345

by Burndy
Catalog ID: YA28A345

Prop 65 Notice

UNINSULATED ALUMINUM COMPRESSION TERMINAL, 1-HOLE
DESIGNUL Listed 90° C600 Volts to 35 KV.



Product Details

General

Connector Type	Terminal
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
UPC	781810562208
UPC 12 Digit	7818105622088

Dimensions

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG
Conductor - Copper Str Compact Size	4/0 AWG
Conductor - Copper Str Compact Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size • CU C Str Cmpnt-Size

Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)