



YA28L4TCG1

by Burndy
Catalog ID: YA28L4TCG1

Prop 65 Notice

Cu terminal(4 hole split pad), 4 Holes/W/insp W, 4/0 AWG, 1/4" stud, , Tin plated, Purple, 15 Index.

Features: Compression Split Pad Terminal, Overall Length: 3.29 IN, Finish: Tin Plated

Product Details

General

Application	For use on copper compression connections
Color Code	Purple
Connector Type	Terminal
Die Index	15
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	4
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810125823
UPC 12 Digit	7818101258233

Dimensions

Dimension - B Length fraction	1.00 in
Dimension - B Length inch	1.00 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - F Width Center to Center inch	0.75 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	84 mm
Dimension - Length Overall inch	3.29 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.69 in
Dimension - Pad Width inch	1.38 in
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size inch	1/4

Dimension - Thread Size	1/4 in
Dimension - Z inch	0.20 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	200 (61) Navy
Conductor - Copper Str Size	4/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)