

YA28L56

by Burndy
Catalog ID: YA28L56

Prop 65 Notice

Cu Comp Terminal Code Cond, Bvl Entry, 1 Hole/W/InspWindow, 4/0 Code, 200 Navy, 600 V-35 kV, 3/4" Stud, Std bbl, Tin Plated, Purple, 15 Index.

45 DEG And 90 DEG Angles Are Available, Tongue Angle: Straight



Product Details

General

Application	For Code Conductor
Color Code	Purple
Connector Type	Terminal
Die Index	15
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810017920
UPC 12 Digit	7818100179200

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.91 in
Dimension - Bolt Size fraction	3/4
Dimension - Hole Size inch	0.81 in
Dimension - Hole Size mm	21 mm
Dimension - L Length Overall mm	74 mm
Dimension - Length Overall inch	2.90 in
Dimension - N inch	0.75 in
Dimension - Outside Diameter inch	0.69 in
Dimension - Pad Width inch	1.05 in
Dimension - Strip Length inch	1-1/8

Dimension - Stud Size fraction	3/4
Dimension - Stud Size inch	3/4
Dimension - Thread Size	3/4 in
Dimension - Z inch	0.77 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	200 (61) Navy
Conductor - Copper Str Size	4/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)