

## YA28LB1LD

by Burndy  
Catalog ID: YA28LB1LD

One hole Cu Compression terminal, Belled end Standard barrel , 3/0 AWG, Lead plated



### Product Details

#### General

Connector Type	Terminal
Die Index	1022
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Lead
Temperature Rating	194
Type	Standard Barrel, Lead Plated
UPC	781810179857
UPC 12 Digit	7818101798577

#### Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - D inch	1.50 in
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	72 mm
Dimension - Length Overall inch	2.85 in
Dimension - N inch	0.56 in
Dimension - Outside Diameter inch	0.69 in
Dimension - Pad Width inch	1.02 in
Dimension - Strip Length inch	1-1/16

Dimension - Z inch	0.91 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	3/0 AWG
Conductor - Copper Str Size Range	3/0 AWG
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	Yes

## Logistics

Minimum Pack Quantity	200
-----------------------	-----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)