

YA28LH82LD90

by Burndy
Catalog ID: YA28LH82LD90

CU HYSEALUG-90 DEG PAD-L



* Representative image

Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Lead
Temperature Rating	194
Type	Shrouded Barrel, Lead Plated
UPC	781810185513
UPC 12 Digit	7818101855133

Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.62 in
Dimension - D inch	1.41 in
Dimension - Hole Size inch	0.42 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	59 mm
Dimension - Length BB inch	0.62 in
Dimension - Length Overall inch	2.34 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	1.00 in
Dimension - Z inch	0.91 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex M Size	2 AWG
Conductor - Copper Flex M Size Range	2 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	No

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)