

YA28LH82LD

by Burndy
Catalog ID: YA28LH82LD

Copper HYLUG™, 1 Hole W/O Inspection Window , 3/0 AWG FLEX, 3/8" stud, Lead Plated



* Representative image

Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Straight
Plated	Yes
Plating Type	Lead
Trade Name	HYLUG™
Type	Shrouded Barrel, Lead Plated
UPC	781810025949
UPC 12 Digit	7818100259499

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	98 mm
Dimension - Length BB inch	0.62 in
Dimension - Length Overall inch	3.83 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	1.00 in
Dimension - Z inch	0.91 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Flex M Size	3/0 AWG
Conductor - Copper Flex M Size Range	3/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	No

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)