

YA28LH94TN

by Burndy
Catalog ID: YA28LH94TN

Copper HYLUG™, 1 Hole W/O Inspection Window , 4/0 AWG FLEX, 5/16" stud, Tin Plated



* Representative image

Product Details

General

Connector Type	Terminal
Die Index	1022
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Straight
Plated	Yes
Plating Type	Tin
Trade Name	HYLUG™
Type	Shrouded Barrel, Tin Plated
UPC	781810137949
UPC 12 Digit	7818101379499

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - Hole Size inch	0.80 in
Dimension - Hole Size mm	20 mm
Dimension - Inside Diameter inch	0.72 in
Dimension - L Length Overall mm	87 mm
Dimension - Length BB inch	0.75 in
Dimension - Length Overall inch	3.44 in
Dimension - N inch	0.53 in
Dimension - Pad Width inch	1.02 in
Dimension - Thread Size	5/16 in
Dimension - Z inch	0.51 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex K Size	3/0 AWG
Conductor - Copper Flex K Size Range	3/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)