

YA28LNT14

by Burndy
Catalog ID: YA28LNT14

Prop 65 Notice

Cu compression narrow tongue std barrel-Code conductor, Single hole/W/ insp window, 4/0 AWG, 1/4" stud, Purple15 index

Features: Compression Narrow Tongue Terminal, UL Listed 90 DEG C, 600 Volts to 35 kV , With Inspection Window, Tongue Angle: Straight, Finish: Tin Plated, Die Index: 15, Wire Strip Length: ,1-1/8 IN



Product Details

General

Application	For Code Conductor
Color Code	Purple
Connector Type	Terminal
Construction Material - Main	Copper tubing
Die Index	15
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	Terminals, HYLUG
Trade Name	HYLUG™
Type	YA-L-NT, Standard Barrel
UPC	781810235089

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - D inch	1.07 in
Dimension - L Length Overall mm	66 mm
Dimension - Length Overall inch	2.60 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.69 in
Dimension - Pad Width inch	0.76 in
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.76 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	200 (61) Navy
Conductor - Copper Str Navy Size Range	200 (61) Navy
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175

1-603-647-5299 (International)