

YA28LNT38D20090

by Burndy
Catalog ID: YA28LNT38D20090

Copper HYLUG™, 1 Hole W/O Inspection Window , 4/0 AWG FLEX, 3/8" stud, Long Barrel, Tin Plated



Product Details

General

| | |
|--------------------------------------|---------------|
| Color Code | Purple |
| Connector Type | Terminal |
| Die Index | 15 |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Physical Attribute - Tongue Type | Straight |
| Plated | Yes |
| Plating Type | Tin |
| Trade Name | HYLUG™ |
| UPC | 781810049440 |
| UPC 12 Digit | 7818100494400 |

Dimensions

| | |
|-----------------------------------|-----------|
| Dimension - B Length fraction | 1 in |
| Dimension - B Length inch | 1.00 in |
| Dimension - Bolt Hole Size inch | 0.39 in |
| Dimension - Bolt Size fraction | 3/8 |
| Dimension - Hole Size inch | 0.40 in |
| Dimension - Hole Size mm | 10 mm |
| Dimension - L Length Overall mm | 70 mm |
| Dimension - Length Overall inch | 2.76 in |
| Dimension - N inch | 0.38 in |
| Dimension - Pad Width inch | 0.72 in |
| Dimension - Strip Length inch | 1-1/16 |
| Dimension - Thread Size | 3/8 |
| Dimension - Z inch | 1.62 in |
| Physical Attribute - Tongue Angle | 90 Degree |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|-----------------------------------|---------|
| Conductor - Copper DLO Size Range | N/A |
| Conductor - Copper Str Size | 4/0 AWG |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-----|
| Minimum Pack Quantity | 100 |
|-----------------------|-----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)