

YA28LNT516

by Burndy
Catalog ID: YA28LNT516

Prop 65 Notice

Cu compression narrow tongue std barrel-Code conductor, single hole/W/ insp window, 600V-35Kv, 5/16" stud, Purple, 15 index



Product Details

General

Color Code	Purple
Connector Type	Terminal
Die Index	15
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810498187

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - D inch	0.77 in
Dimension - L Length Overall mm	53 mm
Dimension - Length Overall inch	2.09 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.69 in
Dimension - Pad Width inch	0.70 in
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size inch	5/16
Dimension - Z inch	0.43 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Solid Size	4/0 AWG
Conductor - Copper Solid Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)