

YA28NT38GTLD

by Burndy
Catalog ID: YA28NT38GTLD

Copper HYLUG™, 1 Hole W/O Inspection Window , 4/0 AWG FLEX, 3/8" stud, Long Barrel, Lead Plated



Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Narrow
Plated	Yes
Plating Type	Lead
Trade Name	HYLUG™
Type	Gas Tight, Lead Plated
UPC	781810044902
UPC 12 Digit	7818100449022

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.51 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	92 mm
Dimension - Length Overall inch	3.62 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	0.94 in
Dimension - Strip Length inch	1-1/8
Dimension - Thread Size	3/8
Dimension - Z inch	0.70 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Flex I Size	4/0 AWG
Conductor - Copper Flex I Size Range	4/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)