

## YA28N

by Burndy  
Catalog ID: YA28N

Prop 65 Notice

Uninsul Cu Comp Terminal Code Cond, Bvl Entry, 1  
Hole/W/O/InspWindow, 4/0 Code, 200 Navy Str, 600 V-35 kV, 1/2" Stud,  
Lng bbl, Purple, 15 Index.

Uninsul Cu Comp Terminal Code Cond, Bvl Entry, 1  
Hole/W/O/InspWindow, 4/0 Code, 200 Navy Str, 600 V-35 kV, 1/2 IN  
Stud, Lng bbl, Purple, 15 Index



## Product Details

### General

Application	For use on copper compression connections
Color Code	Purple
Connector Type	Terminal
Die Index	15
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810282229
UPC 12 Digit	7818102822299

### Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.62 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	82 mm
Dimension - Length Overall inch	3.41 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.69 in
Dimension - Pad Width inch	1.02 in
Dimension - Strip Length inch	1-11/16
Dimension - Thread Size	1/2

Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Navy Size	200 (61) Navy
Conductor - Copper Str Size	4/0 AWG
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)