

## YA292LH122LD

by Burndy  
Catalog ID: YA292LH122LD

Prop 65 Notice

Slotted Cu Compression terminal with Shrouded barrel, 3/8" stud,  
Shrouded Barrel, Lead plated



### Product Details

#### General

Connector Type	Terminal
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Lead
Trade Name	HYLUG™
Type	Shrouded Barrel, Lead Plated
UPC	781810164600
UPC 12 Digit	7818101646000

#### Dimensions

Dimension - B Length fraction	1-15/16 in
Dimension - B Length inch	1.00 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - Inside Diameter inch	0.88 in
Dimension - L Length Overall mm	140 mm
Dimension - Length BB inch	0.63 in
Dimension - Length Overall inch	5.50 in
Dimension - N inch	0.69 in
Dimension - Outside Diameter inch	1.04 in

Dimension - Pad Width inch	1.10 in
Dimension - Z inch	1.05 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	No

## Logistics

Minimum Pack Quantity	200
-----------------------	-----

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)