

YA292LH75CG3

by Burndy
Catalog ID: YA292LH75CG3

Copper HYSEALUG™ 4/0 "M" Lead Plate, 4/0 AWG, 1 Hole, BRITE - DIP LEAD PLATED.



* Representative image

Product Details

General

Connector Type	Terminal
Die Index	29
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Lead
Trade Name	HYLUG™
Type	Shrouded Barrel, Lead Plated
UPC	781810429358
UPC 12 Digit	7818104293588

Dimensions

Dimension - B Length fraction	1-15/16 in
Dimension - B Length inch	1.94 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - Inside Diameter inch	0.86 in
Dimension - L Length Overall mm	141 mm
Dimension - Length BB inch	0.63 in
Dimension - Length Overall inch	5.56 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.01 in
Dimension - Pad Width inch	1.10 in
Dimension - Z inch	1.00 in
Physical Attribute - Tongue Angle	Straight
Thickness	0.16 in

Weight	0.254 lb
--------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex M Size	4/0 AWG
Conductor - Copper Flex M Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)