

YA292LH90

by Burndy
Catalog ID: YA292LH90

Prop 65 Notice

Copper Compression Terminal with shrouded barrel; 2 Holes;250 Kcmil;
Tin Plated



Product Details

General

Category General	Accessories
Color	White
Color Generic	white
Connector Type	Terminal
Construction Material - Main	Plastic
Construction Material -Secondary	steel
Construction Material -Secondary part	mounting bracket
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Finish Name	White
Lamp Included	No
Lifestyle	<ul style="list-style-type: none"> • Modern • Transitional
Material	Copper
Mount location	ceiling
Mounting for outlet box included	No
Photocell	No
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Post top fits standard	No
Power Source	Hardwired
Power Source Required?	Yes
Prewired	No
Style	<ul style="list-style-type: none"> • Modern • Transitional
Sub Brand	Progress LED
Trade Name	HYLUG™
Type	Shrouded Barrel, Tin Plated
UPC	785247189847 781810185537

UPC 12 Digit	7818101855377
Warranty Length	1 year warranty

Dimensions

Depth	4.2 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	165 mm
Dimension - Length BB inch	1.00 in
Dimension - Length Overall inch	6.50 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.75 in
Dimension - Pad Width inch	1.125 in
Dimension - Z inch	0.62 in
Gross Weight with Packaging	0.11 lb
Height	1.3 in
Note Weight of fixture exceeds NEC limits	No
Physical Attribute - Tongue Angle	90 Degree
Weight	0.43 lb
Width	4.3 in
Width Diameter Descriptor	W.

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000
Voltage Rating	120 V

Conductor Related

Conductor - Copper Str Size	250 kcmil
Conductor - Material	Copper

Certifications and Compliance

Americans with Disabilities Act	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
DarkSky	No
EnergyStar	No
JA8	No
Other Heavy Metal Content Indicator	No
Standards - RoHS Compliance Status	CM
Title 20	W
Title 22	No
Title 24	No

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)