

YA292NNT

by Burndy
Catalog ID: YA292NNT

250, LONG, 1/2 NAR. TONG NS



Product Details

General

Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	HYLUG™
UPC	781810672747
UPC 12 Digit	7818106727477

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	250 (61)
Conductor - Copper Str Size	250
Conductor - Copper Str Size Range	250
Conductor Type	<ul style="list-style-type: none">• CU C Str Navy-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)