

YA292NT14

by Burndy
Catalog ID: YA292NT14

Copper Tubing,Narrow,2 Holes W/O insp window,250 kcmil,1/4" stud,Tin plated,Yellow,16 index



Product Details

General

Color Code	Yellow
Connector Type	Terminal
Die Index	16
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810672709

Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.62 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - L Length Overall mm	88 mm
Dimension - Length Overall inch	3.46 in
Dimension - Outside Diameter inch	0.75 in
Dimension - Pad Width inch	0.76 in
Dimension - Strip Length inch	1-11/16 in
Dimension - Stud Size inch	1/4 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

Conductor - Copper Str Navy Size	250 (61)
Conductor - Copper Str Navy Size Range	250 (61)
Conductor - Copper Str Size	250
Conductor - Copper Str Size Range	250
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)