

# YA292NT38E16

by Burndy  
Catalog ID: YA292NT38E16

Copper Tubing,Narrow,2 Holes W/O insp window,250 kcmil,3/8" stud,Tin plated,Yellow,16 index



## Product Details

### General

Color Code	Yellow
Connector Type	Terminal
Die Index	16
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810672730

### Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.62 in
Dimension - Bolt Hole Size inch	0.41 in
Dimension - Bolt Size fraction	3/8
Dimension - L Length Overall mm	121 mm
Dimension - Length Overall inch	4.77 in
Dimension - Outside Diameter inch	0.75 in
Dimension - Pad Width inch	0.76 in
Dimension - Strip Length inch	1-11/16 in
Dimension - Stud Size inch	3/8 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	250 (61)

Conductor - Copper Str Size	250
Conductor - Copper Str Size Range	250
Conductor Type	<ul style="list-style-type: none"><li>• CU C Str-Size</li><li>• CU C Str Navy-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)