



YA292NU90

by Burndy
Catalog ID: YA292NU90

Prop 65 Notice

Blank Tongue Hylug, 250 kcmil, 16 Index

Product Details

General

Color Code	Yellow
Connector Type	Terminal
Die Index	16
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	0
Plated	Y
Plating Type	Electro Tin Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810032787
UPC 12 Digit	7818100327877

Dimensions

Dimension - B Length inch	1.62 in
Dimension - L Length Overall mm	132 mm
Dimension - Length Overall inch	5.21 in
Dimension - Outside Diameter inch	0.75 in
Dimension - Pad Width inch	1.11 in
Dimension - Strip Length inch	1-11/16
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Navy Size	250 (61) Navy
Conductor - Copper Str Navy Size Range	250 (61) Navy

Conductor - Copper Str Size	250 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)