

YA29LBOX

by Burndy
Catalog ID: YA29LBOX

Prop 65 Notice

Copper Compression Lug, 1 Hole w/ Inspection Window, 250 kcmil, 1/2" Stud, Short Barrel, Tin Plated.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Temperature Rating: 90 DEG C, Wire Strip Length: 1-1/8 IN, Die Index: 16, Package: Box, Finish: Electro-Tin Plated, Tongue Angle: Straight, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W29VT Die, (2), X29RT Die, (4), Hydraulic: BCT500HS, Y500CTHS Tool, W29VT, W29RT Die, (2), X29RT Die, (4), Y35, Y39, Y750, PAT750 Tool, U29RT Die, (1), Y46 Tool, U29RT Die With PUADP-1 Adapter, (1), Color Code: Yellow, Dieless Tools (number Of Crimps): Y644HS, MY29-3, MY29-11 Tool, (1), Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (2), Conductor Type: Commercial Stranded Copper



Product Details

General

| | |
|--------------------------------------|---|
| Application | For Code Conductor |
| Color Code | Yellow |
| Connector Type | Terminal |
| Die Index | 16 |
| Feature - Barrel Style | <ul style="list-style-type: none"> • Chamfered • Skived |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Physical Attribute - Tongue Type | Standard |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Sub Brand | HYLUG |
| Temperature Rating | 194 |
| Trade Name | HYLUG™ |
| Type | Standard Barrel, Tin Plated |
| UPC | 781810554500 |
| UPC 12 Digit | 7818105545000 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - B Length inch | 1.06 in |
| Dimension - Bolt Hole Size inch | 0.52 in |
| Dimension - Bolt Size fraction | 1/2 |
| Dimension - D inch | 1.08 in |
| Dimension - Hole Size inch | 0.53 in |
| Dimension - Hole Size mm | 13 mm |
| Dimension - L Length Overall mm | 68 mm |

| | |
|-----------------------------------|----------|
| Dimension - Length Overall inch | 2.67 in |
| Dimension - N inch | 0.53 in |
| Dimension - Outside Diameter inch | 0.75 in |
| Dimension - Pad Width inch | 1.11 in |
| Dimension - Strip Length inch | 1-1/8 |
| Dimension - Stud Size fraction | 1/2 |
| Dimension - Stud Size inch | 1/2 |
| Dimension - Z inch | 0.55 in |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|----------------------------------|---------------|
| Conductor - Copper Str Navy Size | 250 (61) Navy |
| Conductor - Copper Str Size | 250 kcmil |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)