

# YA29LENT38

by Burndy  
Catalog ID: YA29LENT38

Prop 65 Notice

Copper Compression lug, Narrow Tongue, 1 Hole w/ Inspection Window, 250 kcmil, 3/8" Stud, Short Barrel, Tin Plated



## Product Details

### General

Color Code	Yellow
Connector Type	Terminal
Die Index	16
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810080016

### Dimensions

Dimension - B Length fraction	1-1/16 in
Dimension - B Length inch	1.06 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	1.20 in
Dimension - L Length Overall mm	75 mm
Dimension - Length Overall inch	2.96 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.75 in
Dimension - Pad Width inch	0.76 in
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.79 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	250 (61) Navy
Conductor - Copper Str Navy Size Range	250 (61) Navy
Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

## For further technical assistance, please contact us

### BURNDY Headquarters

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)