

# YA29LH75LD

by Burndy  
Catalog ID: YA29LH75LD

One hole Cu Compression terminal, #2 AWG, 3/8" stud, Lead plated



\* Representative image

## Product Details

### General

Connector Type	Terminal
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Lead
Temperature Rating	194
Trade Name	HYLUG™
Type	Shrouded Barrel, Lead Plated
UPC	781810025918
UPC 12 Digit	7818100259188

### Dimensions

Dimension - B Length inch	1.93 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	1.41 in
Dimension - Hole Size inch	0.42 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	96 mm
Dimension - Length BB inch	0.62 in
Dimension - Length Overall inch	3.78 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.04 in
Dimension - Pad Width inch	1.09 in
Dimension - Z inch	0.91 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Flex M Size	2 AWG
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	No

### Logistics

Minimum Pack Quantity	200
-----------------------	-----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)