

# YA29T14BBR

by Burndy  
Catalog ID: YA29T14BBR

HYDENT-250MCM-BELLED BAR



## Product Details

### General

Connector Type	Terminal
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Bright
Temperature Rating	194
UPC	781810181379
UPC 12 Digit	7818101813799

### Dimensions

Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.13 in
Dimension - D inch	1.13 in
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	85 mm
Dimension - Length Overall inch	3.34 in
Dimension - N inch	0.56 in
Dimension - Pad Width inch	1.09 in
Dimension - Z inch	0.57 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Navy Size	250 (61) Navy
----------------------------------	---------------

Conductor - Copper Str Navy Size Range	250 (61) Navy
Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	100
-----------------------	-----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)