

YA2C2NDTS

by Burndy
Catalog ID: YA2C2NDTS

Prop 65 Notice

Cu Tubing Hylug, 2 Holes w/o Inspection Window, #2 AWG Code,60 Navy, 600V-35kV, 1/2" stud, Long, Compression, 0.56 in BCD, Brown.

Die index:10, Long Barrel, Tongue Angle: Straight, STRIP LG: 1-5/16 IN



Product Details

General

Application	For termination of wires
Color Code	Brown
Connector Type	Terminal
Die Index	10
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	YA2NDTS
UPC	781810192146
UPC 12 Digit	7818101921466

Dimensions

Dimension - B Length inch	1.25 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.02 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	118 mm
Dimension - Length Overall inch	4.64 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	1-5/16

Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Navy Size	60 (37) Navy
Conductor - Copper Str Size	2 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)