



## YA2C2

by Burndy  
Catalog ID: YA2C2

Prop 65 Notice

Copper Compression lug, 2 Hole w/o Inspection Window, 2 AWG, 1/3" Stud, 3/4" stud hole spacing, Long Barrel, Tin Plated

## Product Details

### General

Color Code	Brown
Connector Type	Terminal
Die Index	15
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810500705
UPC 12 Digit	7818105007055

### Dimensions

Dimension - B Length inch	1.25 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - D inch	1.59 in
Dimension - Hole Size inch	0.34 in
Dimension - Hole Size mm	9 mm
Dimension - L Length Overall mm	75 mm
Dimension - Length Overall inch	2.97 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Pad Width inch	0.59 in
Dimension - Strip Length inch	1-5/16
Dimension - Z inch	0.50 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Navy Size	60 (37) Navy
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Size	2 AWG
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)