

YA2CT6

by Burndy
Catalog ID: YA2CT6

Prop 65 Notice

Cu Terminal, 1 Hole, #2 Str, 1/2" Stud, 2.74" L, 0.81" W, Tin Plated, Brown, 10 Index.

Features: Compression Terminal, Tongue Angle: Straight, Finish: Tin Plated



Product Details

General

Application	For termination of wires
Color Code	Brown
Connector Type	Terminal
Die Index	10
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin Plated
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	Terminal
UPC	781810017951
UPC 12 Digit	7818100179511

Dimensions

Dimension - B Length inch	1.25 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - D inch	1.12 in
Dimension - Hole Size inch	0.52 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.74 in
Dimension - N inch	0.56 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Pad Width inch	0.81 in
Dimension - Strip Length inch	1-5/16
Dimension - Z inch	0.56 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Solid Size	2 AWG
Conductor - Copper Str Size	2 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)